

ULTRASEAL GEL LINER

A step above.

USHGL | USHGC | USLGL | USLGC | USUGL | USUGC



DESCRIPTION

Introducing the revolutionary UltraSeal gel liner—a groundbreaking product that **seamlessly integrates advanced sealing technology with the superior benefits of gel.**

With an integrated band available at three different heights, users will experience an airtight seal upon socket entry. When combined with OptiGel, this liner offers exceptional comfort and excellent conformity to the residual limb, ensuring a secure and snug fit that enhances control, comfort, and safety.

PART #	SUSPENSION
USHGL/USLGL/USUGL	LOCKING
USHGC/USLGC/USUGC	CUSHION

Recommended for all activity levels.



WHY ULTRA GEL?

1

It's the only sealing liner available in gel.

OptiGel has a smooth, soft texture that ensures gentle skin contact and a tailored fit around the residual limb.

INCREASED COMFORT

2

It's made with less constrictive fabric.

Outer Premium fabric combines strength, durability, and differentiated stretch for comfortable elasticity.

EASY TO DON & DOFF

3


It's available in both locking and cushion.

The locking feature ensures users are provided with a suspension that is secure, firm, and comfortable.


DUAL SUSPENSION

CROSS SECTION DIAGRAM


1 THICKNESS | 3 RING HEIGHT OPTIONS | CUSHION & LOCKING



HIGH ring begins 18 cm from the center of the distal end.




LOW ring begins 13 cm from the center of the distal end.









ULTRA LOW ring begins 8 cm from the center of the distal end.

HOW TO SIZE

Measurements taken 6cm from the distal end



SIZING CHARTS

MEASURED SIZE (CM)	 HIGH RING LOCKING 3MM UNIFORM	 HIGH RING CUSHION 3MM UNIFORM	 LOW RING LOCKING 3MM UNIFORM	 LOW RING CUSHION 3MM UNIFORM	 ULTRA LOW RING LOCKING 3MM UNIFORM	 ULTRA LOW RING CUSHION 3MM UNIFORM
20-23 cm	USHGL20-3	USHGC20-3	USLGL20-3	USLGC20-3	USUGL20-3	USUGC20-3
24-25 cm	USHGL24-3	USHGC24-3	USLGL24-3	USLGC24-3	USUGL24-3	USUGC24-3
26-27 cm	USHGL26-3	USHGC26-3	USLGL26-3	USLGC26-3	USUGL26-3	USUGC26-3
28-31 cm	USHGL28-3	USHGC28-3	USLGL28-3	USLGC28-3	USUGL28-3	USUGC28-3
32-34 cm	USHGL32-3	USHGC32-3	USLGL32-3	USLGC32-3	USUGL32-3	USUGC32-3
35-37 cm	USHGL35-3	USHGC35-3	USLGL35-3	USLGC35-3	USUGL35-3	USUGC35-3
38-43 cm	USHGL38-3	USHGC38-3	USLGL38-3	USLGC38-3	USUGL38-3	USUGC38-3
44-47 cm	USHGL44-3	USHGC44-3	USLGL44-3	USLGC44-3	USUGL44-3	USUGC44-3