


PROSTHETIC LINER SIZING CHARTS

i HOW TO SIZE

Measurements taken 6cm from the distal end



Tel +420 377 223 127 | Fax +420 377 223 010

www.easyliner.eu | info@easyliner.eu

Božkovské náměstí 17/21, 32600 Plzeň – Czech Republic

PART #	DESCRIPTION	THICKNESS (MM)	SIZE								
			16	20	24	26	28	32	35	38	44
AKDT AKDTHD AKFR AKFRHD	Extreme Liner	3 or 6	16	20	24	26	28	32	35	38	44
APDT-TP APFR-TP	Anterior Posterior Tapered Liner	6/3		20	24	26	28	32			
ECDTHD ECFRHD	ECO Liner	3 or 6		20	24	26	28	32	35	38	44
ELDT ELFR	EasyLiner	3, 6, 6/3* or 9*	16	20	24*	26	28*	32	35*	38	44
GPDT GPFR	General Purpose Liner	3 or 6	16	20	24	26	28	32	35	38	44
SPDT SPDTHD SPFR SPFRHD	Superior Performance Liner	3 or 6	16	20	24	26	28	32	35	38	44
SADT SAFR SBFR	Smart Seal SADT	3 or 6		20	24	26	28	32		38	
	Smart Seal SAFR	3 or 6				26	28	32	35	38	
	Smart Seal SBFR	3 or 6		20	24	26	28				
EZF	EasyFlex Liner	3 or 6	16	20	24	26	28	32	35	38	44
VSDT	Liberty Liner	6		20	24	26	28	32		38	
PSI	Proximal Seal Interface	6 or 6/3	16	20	24	26	28	32		38	44
PFGFR PFGDT	ProFit Liner	3 or 6	16	20	24	26	28	32	35	38	44
USHGL USHGC USLGL USLGC USUGL USUGC	UltraSeal Gel Liner	3		20	24	26	28	32	35	38	44**
CIRCUMFERENCE (CM)			16-19	20-23	24-25	26-27	28-31	32-34	35-37	38-44	44-53

*Easyliner: 9mm only available in sizes 24 and 28; size 35 available only in 3mm and 6mm

**UltraSeal size 44 circumference ranges 44-47cm

PART #	DESCRIPTION	THICKNESS (MM)	SIZE										
			20	22	24	26	28	30	32	35	38	41	44
LSC LSL	Silicone Pro Liner	2	20	22	24	26	28	30	32	35	38	41	44
SSGSC SSGSL	SoftSil® Liner	2	20	22	24	26	28	30	32	35	38	41	44
USHGL USHGC USLGL USLGC USUGL USUGC	UltraSeal Silicone Liner	2	20	22	24	26	28	30	32	35	38	41	44
CIRCUMFERENCE (CM)			20-22	22-24	24-26	26-28	28-30	30-32	32-35	35-38	38-41	41-44	44-47

PART #	DESCRIPTION	THICKNESS (MM)	SIZE							
			10	16	20	24	26	28	32	38
ELPX	EasyLiner SuperStretch	6	10	16	20	24	26	28	32	38
CIRCUMFERENCE (CM)			10-15	16-19	20-23	24-25	26-27	28-31	32-37	38-43